

# Модульные поляриметры VariPol

## Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [sup@nt-rt.ru](mailto:sup@nt-rt.ru) || сайт: <https://schmidt-haensch.nt-rt.ru/>



## Modular Polarimeter

The fastest in precision polarimetry, offers unrivaled accuracy, modularity and flexibility for pharmaceutical applications and more

- \* Standard conditions (589 nm,  $t_s=20^\circ\text{C}$ ,  $t_A=23^\circ\text{C}$ )
- \*\* Optional
- \*\*\* Not included in delivery

### Combining over 160 years of experience with the endless strive for innovation

The VariPol takes the proven SCHMIDT + HAENSCH technology to a new level combining it with new innovations and all advantages of the VariFamily. The new design has nearly half the size of our earlier models packed with new features and highly integrated hardware. The experience of more than 160 years in polarimetry is reflected in all components like the fortified Aluminum core, the built in quality indicator of samples as well as the check of calibration standards. The 100mm sample room is optimal for the needs of pharmaceutical and chemical laboratories.



Measurement data				
14.10.2022 14:26	0191721220114	alpha		
SampleID	Ref. #C1	4.00071	Etirubia (Gm)	
0191721220114	13.19000	13.19000	100	2.0
14.10.2022 14:26	0191721220106	alpha		
SampleID	Ref. #C1	4.00071	Etirubia (Gm)	
0191721220106	0.00000	0.00000	100	1.0
14.10.2022 14:26	0191721220104	alpha		
SampleID	Quartz	Sugar	Ref. #C1	
0191721220104	0.01	0.01	0.00000	0.0
14.10.2022 14:26	0191721220104	alpha		
SampleID	Ref. #C1	4.00071	Etirubia (Gm)	
0191721220104	0.00000	0.00000	100	0.0

SPECIFICATIONS	VariPol C	VariPol B
Measurement scales	° Optical rotation, ° Specific rotation, °Z International Sugar Scale, % Concentration (g/mL, g/100mL, g/L), further scales freely definable	
Measuring range	± 89.9°	
Specifications		
Precision	± 0.01° *	± 0.005° *
Repeatability	± 0.01°	± 0.005°
Resolution	0.005°	0.001°
Sensitivity	Up to OD 3	
Wavelength	1 or 2 wavelengths fixed, standard 589 nm, also available 365, 405, 436, 546	
Measuring time	6 to 8 sec. over the entire measuring range	
Measuring tubes	Up to 100 mm length; standard tubes, tubes with funnel or flow through; wetted parts: glass, stainless steel, Hastelloy	
Temperature measurement	Pt1000 sensor (device) / NTC sensor (Quartz control plates and tubes)	
Sample temperature range	10 °C to 40 °C	
Temperature precision / resolution	± 0.1 °C* / 0.01 °C	
Peltier temp. regulation of the sample room	18 °C to 25 °C	10 °C to 40 °C
Temperature stabilization time	25 °C to 20 °C, ± 0.1 °C, in 1 minute (valid for ambient temp. = 20 °C, with tube)	
Light source	LED, interference filter	
Display	7" Touchscreen**, 800 x 480 Pixel	
Operation	Touchscreen**, Keyboard***, Mouse***, Barcode Reader***, Remote via PC/Tablet/Smartphone***	
Interfaces / Communication	Ethernet 10/100/1000, RS232, USB, WLAN**	
Power	VAC 90-265; 50/60 Hz; 150 W max	
Conformity	International Pharmacopoeia, OIML, 21 CFR part 11, ICUMSA, Australian Standard K157	
Dimensions	With display: 430 x 300 x 270 mm (w x d x h); without display: 430 x 300 x 160 mm (w x d x h)	
Highlights	Basic Polarimeter especially designed for pharmaceutical applications; Modularity; Fast measuring; Peltier system for automatic temperature control; easy to calibrate; constant precision over the whole measuringrange, 21 CFR part 11 ready; energy saving durable LEDs; ELN; LIMS ready	

## По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [sup@nt-rt.ru](mailto:sup@nt-rt.ru) || сайт: <https://schmidt-haensch.nt-rt.ru/>