

Высокопроизводительный круговой поляриметр Polartronic V

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: sup@nt-rt.ru || сайт: <https://schmidt-haensch.nt-rt.ru/>



High Performance Polarimeter

Our fully automatic circle polarimeter provides continuous measurements with high accuracy and is designed for various applications

Polarimeter applications

Polarimetry is an instrumental analytical method using the optical activity by inorganic and organic compounds as a non-destructive measure of their concentration in a solution.

Applications often used

- Determination of concentration
- Purity analysis
- Quality control
- Scientific analysis

Typical applications of the models

- Raw-, intermediate and final products of sugar cane and beet processing
- Food (sugar, starch, milk and dairy products)
- Pharmaceuticals (alkaloids, amino acids, organic compounds, vitamins, essential oils etc.)
- Chemicals (organic fluids, biopolymers, synthetic and organic polymers, benzene, acids etc.)
- Research (analysis of molecular structure, investigation of kinetic reactions as function of time, distinction of optical isomers, monitoring changes in concentration of an optically active component in a reaction mixture as in enzymatic scission)

- * Standard conditions
- ** Optional
- *** Certificate on request

SPECIFICATIONS

POLARTRONIC® V

Measurement scales	°Optical rotation, °Specific rotation, °Z International Sugar Scale, % Concentration (g/mL, g/100mL, g/L) up to 1000 scales freely definable
Measuring range	± 360° / ± 259°Z
Resolution	0.001° / 0,01°Z
Precision	± 0.005° / ± 0,015°Z *
Reproducibility	± 0.001° / ± 0,01°Z
Sensitivity	Up to OD 5
Wavelength	1 or 2 wavelengths fixed: 405, 435, 546, 578, 589, 633, 882 nm (others upon request)
Response time	≤ 4 sec. over the entire measuring range
Measuring tubes	Different Models, 10 to 200 mm length Material: glass, stainless steel, acid-proof stainless steel, stainless steel tubes with integrated temperature sensor***
Temperature measurement	NTC sensor for measurement of sample temperature
Range	0 - 99°C
Resolution	0.01°C
Precision	± 0.1°C
Light source	LED, interference filter
Display	7" Touchscreen, 800 x 480 Pixel, 16 Bit colors
Operation	Touchscreen, keyboard**, mouse**, barcode-reader**, remote via PC**
Interface / Communication	RS232 (1x), USB A (4x), USB B (1x), Ethernet (1x), W-LAN/LAN**
Conformity	International Pharmacopoea, OIML, ASTM, ICUMSA, Australian Standard K157
Highlights	New improved hardware for faster operation; 7" conductive touch display as standard; ready to implement "Aquisys 3" operating system offering: intuitive operation, control via smartphone, connection to third party instruments, industrial standard interfaces, internal data base function, internal 21 CFR Part 11 software
Weight / dimensions	18.3 kg; 730 x 370 x 160 mm (width x depth x height)

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: sup@nt-rt.ru || сайт: <https://schmidt-haensch.nt-rt.ru/>