

Многоволновой рефрактометр АТR L

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: sup@nt-rt.ru || сайт: <https://schmidt-haensch.nt-rt.ru/>



Refractometer

Our spectral-refractometer for automatic dispersion measurements at seven wavelengths over the full visible range

Refractometer applications

The applications of Refractometers are highly diverse for fast and non-destructive determination of refractive index.

Applications often used

- Determination of product purity
- Quality control
- Product fingerprinting
- Optical material characterization

Typical applications of the model

- Measurement of dispersion and calculation of Abbé number
- Measurement of lenses made of plastic or glass
- Quality control of hydrophobic and hydrophilic intraocular lenses (IOL)
- Standard test method for refractive index and refractive index dispersion determination of hydrocarbon liquids according to ASTM 1218
- Testing of fiber-optic components
- Material engineering of polymer compounds

SPECIFICATIONS

ATR L

Measuring scales	Refractive index (RI)
Measuring range	1.33200 - 1.70000 RI* / 100% Brix
Resolution	0.00001 RI* / 0.01% Brix
Precision	± 0.00004 RI* / ± 0.03% Brix
Reproducibility	± 0.00004 RI* / ± 0.03% Brix
Measuring time per sample	20 sec for all 7 wavelength after temperature stabilisation; single sample measurement
Ambient temperature	+ 15° to + 40°C
Automatic temperature compensation	Solid state Peltier-thermostatisation
Operational temperature	+ 10°C to + 80°C
Temperature stability	0.01°C
Temperature precision	± 0.03°C
Detector	CCD-linear array with 2048 elements
Sample compartment	Used materials: stainless steel, Black Delrin®, Teflon®, Viton®, FFKM sealing
Prism	YAG
Light source / Wavelength	7 discrete LED's with fixed wavelengths 400, 450, 490, 545, 590, 660, 700 nm (others on request), wavelength accuracy ± 2 nm
Display	LCD, 16 x 16 characters, back illuminated
Operation	20 key membrane including function keys
Interfaces / Communication	1 x RS232 C, 1x parallel, USB optional
Standards	European and international Pharmacopoeia, various ASTM, ISO and DIN standards
Dimensions / Weight	Mesuring head, stainless steel: 260 x 190 x 220 mm (w x h x d); control unit: 220 x 110 x 290 mm (w x h x d); complete unit 8 kg
Highlights	Automatic dispersion measurement at 7 wavelengths over the full range of visible light (intermediate values interpolated)**; Powerful, internal Peltier temperature control guarantees the fastest measurements with highest accuracy; Aquisys 2 compatible; 21 CFR Part 11 compliant

* Standard conditions (589 nm, 20°C)

** Automatic Abbé number measurement

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: sup@nt-rt.ru || сайт: <https://schmidt-haensch.nt-rt.ru/>