

# Высокопроизводительный рефрактометр АТR Р

## Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [sup@nt-rt.ru](mailto:sup@nt-rt.ru) || сайт: <https://schmidt-haensch.nt-rt.ru/>



# High Performance Refractometer

The robust critical angle refractometer, designed for the sugar industry and mixing ratio determination complemented by a VariControl unit

## Refractometer applications

The applications of Refractometers are highly diverse.

### Applications often used

- Determination of refractive index
- Determination of dry substance
- Determination of mass percent
- Brix measurement
- Standard scale (Brix) with automatic temperature compensation
- Qualitative analysis – identification of samples
- Quantitative analysis of dissolved solids in water or other solvents
- Quantitative analysis of sugars, solves, glycol, oechsle...

### Typical applications of the model

- Sugar industry (main application)
- Beverages (juices with pulp)
- Samples with suspended particles
- Food (oil from palm, corn, sunflower, soya)

## SPECIFICATIONS

## ATR-P

<b>Measuring scales</b>	Refractive Index (RI), Sucrose (%Brix) Up to 1000 scales freely definable
<b>Measuring range</b>	1.33200 - 1.54000 RI / 0 - 100% Brix
<b>Resolution</b>	0.00001 RI / 0.01% Brix
<b>Precision</b>	± 0,00002 RI / ± 0.02% Brix
<b>Reproducibility</b>	± 0.00001 RI / ± 0.01% Brix
<b>Ambient temperature</b>	+ 10° to + 40°C
<b>Automatic temperature compensation</b>	+ 5° to + 50°C
<b>Temperature measurement</b>	NTC sensor for measurement of sample temperature placed inside the prism
<b>Temperature control Temperature range</b>	Temperature control prism / sample by external water bath 5°C / 50°C
<b>Measurement mode</b>	Single sample or flow through measurement / horizontal or vertical usage
<b>Prism</b>	Sapphire
<b>Light source / wavelength</b>	LED, interference filter 589 nm
<b>Display</b>	VariControl, 7" Touchscreen, 800 x 480 Pixel, 16 Bit colors
<b>Operation</b>	Touchscreen, keyboard**, mouse**, barcode reader**, remote via PC**
<b>Interfaces</b>	1 x RS232 C serial, 3 x USB (A), 1 x USB (B), 1 x Ethernet, Easy connection of keyboard, mouse, printer, barcode reader, PC and network
<b>Conformity</b>	International Pharmacopoea, ASTM, AOAC, DIN, FDA, ICUMSA and others
<b>Highlights</b>	Robust stainless steel measuring head for rough environments; high performance and accuracy; continuous measurement; ESH <sup>1</sup> chamber; MBS <sup>2</sup> as stand alone with VariControl or polarimeter; easy calibration; GLP/GMP; With the VariControl: Maintenance friendly by remote diagnostic; intuitive user handling guided OP system; installation wizard; full traceability of records; ext. LIMS integration <sup>1</sup> Easy sample handling; <sup>2</sup> Modular build-in-system
<b>Weight / dimensions</b>	Measuring Head: 4.5 kg; 200 x 160 x 135 mm (width x depth x height) VariControl: 2.0 kg; 250 x 170 x 180 mm (width x depth x height)

\* Standard conditions (589nm, 20°C)

\*\* Optional

## По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04  
Ангарск (3955)60-70-56  
Архангельск (8182)63-90-72  
Астрахань (8512)99-46-04  
Барнаул (3852)73-04-60  
Белгород (4722)40-23-64  
Благовещенск (4162)22-76-07  
Брянск (4832)59-03-52  
Владивосток (423)249-28-31  
Владикавказ (8672)28-90-48  
Владимир (4922)49-43-18  
Волгоград (844)278-03-48  
Вологда (8172)26-41-59  
Воронеж (473)204-51-73  
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06  
Ижевск (3412)26-03-58  
Иркутск (395)279-98-46  
Казань (843)206-01-48  
Калининград (4012)72-03-81  
Калуга (4842)92-23-67  
Кемерово (3842)65-04-62  
Киров (8332)68-02-04  
Коломна (4966)23-41-49  
Кострома (4942)77-07-48  
Краснодар (861)203-40-90  
Красноярск (391)204-63-61  
Курск (4712)77-13-04  
Курган (3522)50-90-47  
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13  
Москва (495)268-04-70  
Мурманск (8152)59-64-93  
Набережные Челны (8552)20-53-41  
Нижний Новгород (831)429-08-12  
Новокузнецк (3843)20-46-81  
Ноябрьск (3496)41-32-12  
Новосибирск (383)227-86-73  
Омск (3812)21-46-40  
Орел (4862)44-53-42  
Оренбург (3532)37-68-04  
Пенза (8412)22-31-16  
Петрозаводск (8142)55-98-37  
Псков (8112)59-10-37  
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15  
Рязань (4912)46-61-64  
Самара (846)206-03-16  
Санкт-Петербург (812)309-46-40  
Саратов (845)249-38-78  
Севастополь (8692)22-31-93  
Саранск (8342)22-96-24  
Симферополь (3652)67-13-56  
Смоленск (4812)29-41-54  
Сочи (862)225-72-31  
Ставрополь (8652)20-65-13  
Сургут (3462)77-98-35  
Сыктывкар (8212)25-95-17  
Тамбов (4752)50-40-97  
Тверь (4822)63-31-35

Тольятти (8482)63-91-07  
Томск (3822)98-41-53  
Тула (4872)33-79-87  
Тюмень (3452)66-21-18  
Ульяновск (8422)24-23-59  
Улан-Удэ (3012)59-97-51  
Уфа (347)229-48-12  
Хабаровск (4212)92-98-04  
Чебоксары (8352)28-53-07  
Челябинск (351)202-03-61  
Череповец (8202)49-02-64  
Чита (3022)38-34-83  
Якутск (4112)23-90-97  
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: [sup@nt-rt.ru](mailto:sup@nt-rt.ru) || сайт: <https://schmidt-haensch.nt-rt.ru/>